



Hair Color - REDKEN

COLOR FUSION

cream color high performance - with protein



REDKEN
5TH AVENUE NYC

✉ bbazar@globelife.com

☎ +39 0331 1706328



COLOR FUSION

cream color high performance - with protein

staining from innovative gel-cream texture that contains a protein balanced formulation based on amino acids and vegetable protein.

Colorbond Technology, Redken exclusive technology, allows the molecules of pigments and proteins to penetrate to the heart of the hair : the result is a full color, bright, with greenish -dimensional and multi-faceted and a hair more healthy.

COLOR FUSION has a fruity blueberry fragrance and guarantees:

- A perfect coverage of white hair (100%) with complete naturalness and uniformity of result
- A lightening of up to three tones
- Very light blond, smooth, bright, with a lightening of up to 4 shades with the series superschiarente
- A vital and lasting color : thanks to its formulation, it is resistant to repeated washing, UV rays and exposure to light
- A versatile application by using the brush or applicator bottle. The particular texture cream -gel also allows a realization safe and controlled in terms of adherence of the product

shades : COLOR FUSION is a collection of rich and creative. It consists of 5 series, each of which includes multiple ranges.

- NB NATURAL BALANCED ASH / blue, ASH / green, ASH / violet, NEUTRAL, GOLD / beige.
- NF NATURAL FASHION: GOLD / violet, GOLD / gold, GOLD / orange, GOLD / red, BROWN / copper, BROWN / red, COPPER / red.
- F FASHION.
- TITANIUM.
- DF DOUBLE FUSION: BROWNS, REDS and BLONDES.
- NEW RUBILANE : GOLD / copper, COPPER / brown, COPPER / copper. Un'intesità with copper hues and unique life, thanks to the unique pigment RUBILAINE

method of use : COLOR FUSION mixed with an equal dose of Pro -oxide Developer (1:1 ratio). For DOUBLE FUSION the mixture ratio is 1:2. Leave on for 35 minutes at room temperature ranges for AC, NB, NF, F, DF Browns and Reds. For Highlift Blondes DF and the shutter speed is 45 minutes

package : 60 ml tube astucciato